


DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M6X55



Article number	08250.060.055
Brand	-
UBB	950351601428
UNSPSC	31161612
EAN	8715492554925
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
The property class of the corresponding nuts is |4| as a minimum. Depending the supplier material class can differ (4.6 or 4.8)


Standards

DIN	603/555
ISO	≈8677/4034
NF	≈E27-351/E25-402
NEN	≈303/697
BS	≈4933/3692

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
dk (max.)	16.55
k (max.)	3.88
L (mm)	55
m	5
P	1
fn (max.)	4.6

Technical Drawing



s

10

Vn (max.)

6.48

