

Hexagon head bolt for pressure vessels ISO 4014 Steel (AD-W7) Zinc plated 5.6 M10X50

Article number	08751.100.050
Brand	-
UBB	500648335155
UNSPSC	31161620
EAN	8717077214675
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	5.6
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel (AD-W7)
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NEN	1555
NF	E25-112

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	50
P	1.5
s	17

Technical Drawing

