

Hexagon nut turned MF left hand thread DIN 934 Free-cutting steel Plain |6| M12X1,25 (LH)

Article number	11007.120.125
Brand	-
UBB	950355710902
UNSPSC	31161727
EAN	8715492567529
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	6
Driving features	Hexagon
Material	Free-cutting steel
Thread direction	Left (LH)
Surface treatment	Plain
Thread	Metric fine thread
Info	left hand thread

Standards

DIN	934
NEN	1560
NF	E25-401

Technical Specification

d-D	M12
m	10
P	1.25
s	19

Technical Drawing

