

Hexagon nut left hand thread
DIN 934 Steel Zinc plated |8|
M5 (LH)

Article number	11042.050.001
Brand	-
UBB	950355777091
UNSPSC	31161727
EAN	8715492568144
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M5
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Left (LH)
Surface treatment	Zinc plated
Thread	Metric thread
Info	left hand thread

Standards

NF	E25-401
DIN	934
NEN	1560

Technical Specification

d-D	M5
m	4
P	0.8
s	8

Technical Drawing

