

Hexagon nut left hand thread DIN 934 Steel Zinc plated |8| M12 (LH)

Article number	11042.120.001
Brand	-
UBB	950355613726
UNSPSC	31161727
EAN	8715492568182
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Left (LH)
Surface treatment	Zinc plated
Thread	Metric thread
Info	left hand thread

Standards

DIN	934
NEN	1560
NF	E25-401

Technical Specification

d-D	M12
m	10
P	1.75
s	19

Technical Drawing

