

Hexagon nut left hand thread DIN 934 Steel Zinc plated |8| M20 (LH)

Article number	11042.200.001
Brand	-
UBB	500645164335
UNSPSC	31161727
EAN	8717077067066
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M20
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Left (LH)
Surface treatment	Zinc plated
Thread	Metric thread
Info	left hand thread

Standards

NF	E25-401
DIN	934
NEN	1560

Technical Specification

d-D	M20
m	16
P	2.5
s	30

Technical Drawing

