



Hexagon thin nut MF DIN 439 2 Steel Zinc plated 04 M12X1,25

Article number	11380.120.125
Brand	-
UBB	950355091402
UNSPSC	31161727
EAN	8715492571328
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric fine thread

Standards

ASME	B18.2.4.5M
ISO	8675
NF	E25-453
DIN	439-2
NEN	2334-B

Technical Specification

d-D	M12
m	6
P	1.25
s	19

Technical Drawing

