



Self-clinching flush head stud Steel Zinc plated M2,5X12

Article number	14425.025.012
Brand	-
UBB	500656722013
UNSPSC	31161816
EAN	8712423026360
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	2.5 mm
Length	12 mm
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

Technical Specification

d-D	2.5
D	4.1
H (max.)	1.95
Hole size	2.5
L (mm)	12
Min. distance sheet edge	5.4
Min. recommended sheet thickness	1

Technical Drawing

