



Eye bolt DIN 444 B Steel Zinc plated 4.6 M10X50

Article number	16181.100.050
Brand	-
UBB	500647858637
UNSPSC	31161610
EAN	8717077275614
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	444-B
-----	-------

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L≤125mm	26
d-D	M10
d2(H9)	10
d3 (max.)	20
L (mm)	50
P	1.5
s (max.)	12

Technical Drawing

