



**Knurled thumb screw thin  
type DIN 653 Steel Plain  
M4X10**

|                |               |
|----------------|---------------|
| Article number | 16659.040.010 |
| Brand          | -             |
| UBB            | 500649315172  |
| UNSPSC         | 31161500      |
| EAN            | 8717077262140 |
| PKG. of 50     | Full Box Only |

**Technical Parameters**

|                   |               |
|-------------------|---------------|
| Diameter          | M4            |
| Length            | 10 mm         |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

**Standards**

|     |     |
|-----|-----|
| DIN | 653 |
|-----|-----|

**Technical Specification**

|                    |     |
|--------------------|-----|
| d-D                | M4  |
| dk                 | 16  |
| e                  | 3   |
| Full thread if L ≤ | 16  |
| k                  | 3.5 |
| L (mm)             | 10  |
| P                  | 0.7 |

**Technical Drawing**

