



Slotted set screw with cone point DIN 553 Steel Plain 14H M10X50

Article number	20030.100.050
Brand	-
UBB	950351719584
UNSPSC	31161505
EAN	8715492603203
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	14H
Driving features	Slotted
Material	Steel
Thread direction	Right
Point	Cone
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	7434
NF	E25-161
NEN	1488
BS	4219
DIN	553

Technical Specification

d-D	M10
dt (max.)	2.5
L (mm)	50
n	1.6
P	1.5

Technical Drawing

