



## Threaded rod length 1 meter oversized thread DIN 976-1A Steel Hot dip galvanized 8.8 M12

Article number	20150.120.001
----------------	---------------

Brand	-
-------	---

UBB	950353603042
-----	--------------

UNSPSC	31161618
--------	----------

EAN	8715492604712
-----	---------------

PKG. of 5	Full Box Only
-----------	---------------

### Technical Parameters

Length (L) (mm)	1000
-----------------	------

Diameter (d-D)	M12
----------------	-----

Class	8.8
-------	-----

Extra info	1 meter oversized
------------	-------------------

Material	Steel
----------	-------

Thread direction	Right
------------------	-------

Surface treatment	Hot dip galvanized
-------------------	--------------------

Thread	Metric thread
--------	---------------

Info	Oversized hot dip galvanized threaded rods are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized).
------	--

### Standards

DIN	976-1A
-----	--------

NF	E25-136
----	---------

**Technical Specification**

**Technical Drawing**

P

1.75

**FABORY** *OF COURSE.*  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS

