



Threaded rod length 1 meter oversized thread DIN 976-1A Steel Hot dip galvanized 8.8 M27

Article number 20150.270.001

Brand -

UBB 950353602705

UNSPSC 31161618

EAN 8715492604750

PKG. of 2 Full Box Only

Technical Parameters

Length (L) (mm) 1000

Diameter (d-D) M27

Class 8.8

Extra info 1 meter oversized

Material Steel

Thread direction Right

Surface treatment Hot dip galvanized

Thread Metric thread

Info
Oversized hot dip galvanized threaded rods are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized).

Standards

NF E25-136

DIN 976-1A

Technical Specification

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

