



Threaded rod length 1 meter oversized thread DIN 976-1A Steel Hot dip galvanized 8.8 M33

| | |
|----------------|---------------|
| Article number | 20150.330.001 |
| Brand | - |
| UBB | 950353602887 |
| UNSPSC | 31161618 |
| EAN | 8715492604774 |
| PKG. of 2 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | M33 |
| Length | 1000 mm |
| Class | 8.8 |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Hot dip galvanized |
| Thread | Metric thread |

Info

Oversized hot dip galvanized threaded rods are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). 1 meter oversized

Standards

| | |
|-----|---------|
| NF | E25-136 |
| DIN | 976-1A |

| | |
|--------|------|
| d-D | M33 |
| L (mm) | 1000 |
| P | 3.5 |

