



M10 DIN 976-1A Threaded Rod, Self Colour 4.8, 1m

Article number	20200.100.001
Brand	-
UBB	950353006238
UNSPSC	31161618
EAN	8715492605184
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M10
Length	1000 mm
Class	4.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	1 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M10
L (mm)	1000
P	1.5

Technical Drawing

