



M10 DIN 976-1A Threaded Rod, BZP 8.8, 1m

|                |               |
|----------------|---------------|
| Article number | 20230.100.001 |
| Brand          | -             |
| UBB            | 950353012665  |
| UNSPSC         | 31161618      |
| EAN            | 8715492605825 |
| PKG. of 10     | Full Box Only |

Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M10           |
| Length            | 1000 mm       |
| Class             | 8.8           |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |
| Info              | 1 meter       |

Standards

|     |         |
|-----|---------|
| NF  | E25-136 |
| DIN | 976-1A  |

Technical Specification

|        |      |
|--------|------|
| d-D    | M10  |
| L (mm) | 1000 |
| P      | 1.5  |

Technical Drawing

