



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1/2X60 (2.3/8)

Article number	22085.127.060
Brand	-
UBB	500578756974
UNSPSC	31161619
EAN	8715494376624
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1/2 Inch
Length	60 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Technical Specification

B	0.875
---	-------

Technical Drawing

L (mm)	60
M	12.3

