



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1/2X65 (2.1/2)

Article number	22085.127.063
Brand	-
UBB	500578757055
UNSPSC	31161619
EAN	8715494376631
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	1/2 Inch
Length	65 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

### Technical Specification

B	0.875
---	-------

### Technical Drawing

L (mm)	65
M	12.3

