



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1/2X165 (6.1/2)

| | |
|----------------|---------------|
| Article number | 22085.127.165 |
| Brand | - |
| UBB | 500578759036 |
| UNSPSC | 31161619 |
| EAN | 8715494376839 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|-------------------------|
| Diameter | 1/2 Inch |
| Length | 165 mm |
| Class | Gr.B7M - Gr.2HM |
| Material | Steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Unified National Coarse |
| Threads per inch | 13 |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|---------------|
| ASTM | A193/A194 |
| BS | ≈4882 |
| ASME | B16.5/B18.2.2 |

Technical Specification

| | |
|---|-------|
| B | 0.875 |
|---|-------|

Technical Drawing

L (mm) 165

M 12.3

