



**Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 5/8X290 (11.3/8)**

Article number	22085.158.290
Brand	-
UBB	500578765397
UNSPSC	31161619
EAN	8715494379960
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	5/8 Inch
Length	290 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

**Standards**

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

**Technical Specification**

B	1.0625
---	--------

**Technical Drawing**

L (mm)	290
M	15.5

