



Double end stud with reduced shank with 2 hexagon nuts DIN 2510 L/ NF Steel 21CrMoV5-7+QT (1.7709)/25CrMo4+QT (1.7218) Plain M12X100

Article number	23530.120.100
Brand	-
UBB	500644894825
UNSPSC	31161619
EAN	8717077038882
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	100 mm
Marking	GA/KG
Material	Steel
Material technical	21CrMoV5-7+QT (1.7709)/25CrMo4+QT (1.7218)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	External thread with large clearance according to DIN 2510-2.

Standards

DIN	2510-L/NF
-----	-----------

Technical Specification

b	20
d-D	M12
d2	8.5
L (mm)	100
m	12
P	1.75

Technical Drawing



