



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M5X50

Article number	24520.050.050
Brand	-
UBB	950353118447
UNSPSC	31161504
EAN	8715492630780
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ASME	≈B18.6.7M
NF	≈E25-127
ISO	≈1207
DIN	84
BS	≈4183

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	50
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing