



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M5X55

Article number	24520.050.055
Brand	-
UBB	951353041290
UNSPSC	31161504
EAN	8715492630797
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	55 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
NF	≈E25-127
NEN	≈1602
BS	≈4183
ASME	≈B18.6.7M
DIN	84

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	55
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing