



**Slotted cheese head screw
DIN 84 Steel Zinc plated 4.8
M5X70**

Article number	24520.050.070
Brand	-
UBB	950353118694
UNSPSC	31161504
EAN	8715492630827
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
BS	≈4183
NEN	≈1602
NF	≈E25-127
DIN	84
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	70
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing