



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X10

Article number	24520.060.010
Brand	-
UBB	950353119015
UNSPSC	31161504
EAN	8715492630865
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	10
n	1.6
P	1
t (min.)	1.6

Technical Drawing