



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X16

Article number	24520.060.016
Brand	-
UBB	950353119270
UNSPSC	31161504
EAN	8715492630896
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
NEN	≈1602
BS	≈4183
NF	≈E25-127
ISO	≈1207
ASME	≈B18.6.7M

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	16
n	1.6
P	1
t (min.)	1.6

Technical Drawing