



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X60

Article number	24520.060.060
Brand	-
UBB	950353335090
UNSPSC	31161504
EAN	8715492630995
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
ISO	≈1207
BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
NF	≈E25-127

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	60
n	1.6
P	1
t (min.)	1.6

Technical Drawing