



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X40

Article number	24520.080.040
Brand	-
UBB	950353121235
UNSPSC	31161504
EAN	8715492631213
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ISO	≈1207
DIN	84
NF	≈E25-127
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	40
n	2
P	1.25
t (min.)	2

Technical Drawing