



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X60

Article number	24520.080.060
Brand	-
UBB	950353121565
UNSPSC	31161504
EAN	8715492631251
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ISO	≈1207
DIN	84
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-127

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	60
n	2
P	1.25
t (min.)	2

Technical Drawing