



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M10X16

Article number	24520.100.016
Brand	-
UBB	950353121987
UNSPSC	31161504
EAN	8715492631343
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
NF	≈E25-127
NEN	≈1602
DIN	84
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	16
Full thread if L ≤	40
k (max.)	6
L (mm)	16
n	2.5
P	1.5
t (min.)	2.5

Technical Drawing