



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M10X50

Article number	24520.100.050
Brand	-
UBB	950353122555
UNSPSC	31161504
EAN	8715492631428
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈1207
NF	≈E25-127
DIN	84
NEN	≈1602
ASME	≈B18.6.7M

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	16
Full thread if L ≤	40
k (max.)	6
L (mm)	50
n	2.5
P	1.5
t (min.)	2.5

Technical Drawing