



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M10X60

Article number	24520.100.060
Brand	-
UBB	950353122639
UNSPSC	31161504
EAN	8715492631442
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈1602
BS	≈4183
NF	≈E25-127
ISO	≈1207
DIN	84

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	16
Full thread if L ≤	40
k (max.)	6
L (mm)	60
n	2.5
P	1.5
t (min.)	2.5

Technical Drawing