



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M12X25

Article number	24520.120.025
Brand	-
UBB	950353123132
UNSPSC	31161504
EAN	8715492631510
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-127
DIN	84
NEN	≈1602

Technical Specification

d-D	M12
Thread length (min.)	38
dk (max.)	18
Full thread if L ≤	40
k (max.)	7
L (mm)	25
n	3
P	1.75
t (min.)	3

Technical Drawing