



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M12X40

Article number	24520.120.040
Brand	-
UBB	950353123470
UNSPSC	31161504
EAN	8715492631541
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈1602
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183

Technical Specification

d-D	M12
Thread length (min.)	38
dk (max.)	18
Full thread if $L \leq$	40
k (max.)	7
L (mm)	40
n	3
P	1.75
t (min.)	3

Technical Drawing