



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M12X60

Article number	24520.120.060
Brand	-
UBB	950353123629
UNSPSC	31161504
EAN	8715492631572
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ASME	≈B18.6.7M
NF	≈E25-127
DIN	84
ISO	≈1207
BS	≈4183

Technical Specification

d-D	M12
Thread length (min.)	38
dk (max.)	18
Full thread if L ≤	40
k (max.)	7
L (mm)	60
n	3
P	1.75
t (min.)	3

Technical Drawing