

Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M12X80



Article number	24520.120.080
Brand	-
UBB	950353123884
UNSPSC	31161504
EAN	8715492631596
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	80
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183

Technical Specification

Thread length (min.)	38
d_k (max.)	18
Full thread if $L \leq$	40
k (max.)	7
n	3
P	1.75
t (min.)	3

Technical Drawing

