

## Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2X25



Article number 24540.020.025

Brand -

UBB 950353129584

UNSPSC 31161504

EAN 8715492632531

PKG. of 200 Full Box Only

### Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	25
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183

### Technical Specification

Thread length (min.)	16
$d_k$ (max.)	3.8
Full thread if $L \leq$	18
$k$ (max.)	1.2
$n$	0.5
$P$	0.40
$t$ (min.)	0.4

### Technical Drawing

