

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2,5X4



Article number	24540.025.004
Brand	-
UBB	950353129741
UNSPSC	31161504
EAN	8715492632593
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M2,5
Length (L) (mm)	4
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
DIN	963
ASME	≈B18.6.7M
ISO	≈2009

Technical Specification

Thread length (min.)	18
d_k (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

