



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X4

Article number	24540.030.004
Brand	-
UBB	950353130897
UNSPSC	31161504
EAN	8715492632814
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2370
ISO	≈2009
ASME	≈B18.6.7M
DIN	963
NF	≈E25-123

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	4
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

