



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X6

Article number	24540.030.006
Brand	-
UBB	950353131051
UNSPSC	31161504
EAN	8715492632838
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
NEN	≈2370
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	6
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

