



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X25

Article number	24540.030.025
Brand	-
UBB	950353131622
UNSPSC	31161504
EAN	8715492632920
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
DIN	963
NEN	≈2370
ISO	≈2009

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	25
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

