



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X30

Article number	24540.030.030
Brand	-
UBB	950353131705
UNSPSC	31161504
EAN	8715492632944
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	30
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

