



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3,5X30

Article number	24540.035.030
Brand	-
UBB	950353133370
UNSPSC	31161504
EAN	8715492633132
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
DIN	963
NF	≈E25-123
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009

Technical Specification

d-D	M3.5
Thread length (min.)	20
dk (max.)	6.5
Full thread if $L \leq$	25
k (max.)	1.93
L (mm)	30
n	0.8
P	0.6
t (min.)	0.7

Technical Drawing

