

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M4X10



Article number 24540.040.010

Brand -

UBB 950353133784

UNSPSC 31161504

EAN 8715492633194

PKG. of 200 Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	10
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
BS	≈4183
DIN	963
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	22
d_k (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
n	1
P	0.70
t (min.)	0.8

Technical Drawing

