



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M4X25

Article number	24540.040.025
Brand	-
UBB	950353134105
UNSPSC	31161504
EAN	8715492633262
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
ISO	≈2009
DIN	963
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	25
n	1
P	0.7
t (min.)	0.8

Technical Drawing

