



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X50

Article number	24540.050.050
Brand	-
UBB	950353136266
UNSPSC	31161504
EAN	8715492633507
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NEN	≈2370
DIN	963
ISO	≈2009
NF	≈E25-123

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	50
n	1.2
P	0.8
t (min.)	1

Technical Drawing

