



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X60

Article number	24540.050.060
Brand	-
UBB	950353136340
UNSPSC	31161504
EAN	8715492633521
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
BS	≈4183
NEN	≈2370
NF	≈E25-123
ISO	≈2009

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	60
n	1.2
P	0.8
t (min.)	1

Technical Drawing

