



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X90

Article number	24540.060.090
Brand	-
UBB	950353747682
UNSPSC	31161504
EAN	8715492633774
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	90 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-123
ISO	≈2009
DIN	963
NEN	≈2370
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	90
n	1.6
P	1
t (min.)	1.2

Technical Drawing

