



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M8X16

Article number	24540.080.016
Brand	-
UBB	950353138403
UNSPSC	31161504
EAN	8715492633835
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
NEN	≈2370
ISO	≈2009
NF	≈E25-123
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	16
n	2
P	1.25
t (min.)	1.6

Technical Drawing

