



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X45

Article number	24540.100.045
Brand	-
UBB	950353630680
UNSPSC	31161504
EAN	8715492634078
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
NF	≈E25-123
DIN	963
NEN	≈2370
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	45
n	2.5
P	1.5
t (min.)	2

Technical Drawing

